


VELP Scientifica Solutions for JAR/Leaching Test




JLT 4



JLT 6



FC4S



FC6S



FP4

Number of positions		4	6	4	6	4 (portable)
Independent positions				•	•	
Speed settings rpm		from 10 to 300	from 10 to 300	10-15-30-45-60-90-120-150-200	10-15-30-45-60-90-120-150-200	20-40-50-100-200
Time settings		0÷999 minutes	0÷999 minutes	-	-	0÷30 minutes
		0÷99 hours	0÷99 hours	-	-	-
		continuous	continuous	continuous	continuous	continuous
Disconnectable light		backlight	backlight	backlight	backlight	central light
Dimensions (WxHxD) mm		645x347x260	935x347x260	645x347x260	935x347x260	250x320x250
	(in)	(25.4x13.7x10.2)	(36.8x13.7x10.2)	(25.4x13.7x10.2)	(36.8x13.7x10.2)	(9.8x12.6x9.8)
Weight	Kg	13.0	17.0	12.5	18.0	4.8
	(lb)	(28.6)	(37.4)	(27.5)	(39.6)	(10.6)
Power Supply		100÷240 V	100÷240 V	100÷240 V	100÷240 V	100÷240 V
Power		11 W	19 W	18 W	23 W	6 W



www.velp.com