



### Interior protected

Possible static charges are prevented by a dissipation system.



**Explosion protection - Zone 2** 

The interior is free from ignition sources.

# LABEX® 520/720

# 

























#### **■** PRO-ACTIVE- Control:

Permanent, proactive monitoring of the performance data and alerts in the case of deviations – so that you can take countermeasures in good time before a fault threatens your chilled goods; world's most accurate temperature control in refrigerated areas thanks to two standard PT-1000 sensors.

- External housing made from galvanised sheet steel (rustproof), with white, anti-scratch powder coating. Length of the plug cable: approx. 3 m.
- Equipped with castors.
- Interior made from smooth aluminium with colourless protective coating. Gibs (every 15 mm) for flexible interior arrangement.
- Interior consists of five shelves on brackets.
- **Extra-thick 70-mm insulation**, made from high-quality, compression-moulded and environmentally friendly material. Energy saving.
- Self-closing door with easy-to-replace plastic magnetic seal frame, lockable.
- Door hinge on the right-hand side as standard (see illustration), or the left-hand side, can be retrofitted.
- Forced-air cooling, switches off automatically when you open the door, ensures a uniform temperature and minimizes temperature deviations.

- Valve controlled pressure compensation for easier door
- Automatic fast defrosting with time limit and temperature monitoring. Defrost sensors are protected by safety
- Removable condensation container.
- Power failure alarm (visual and audible alarm), the monitoring unit remains in operation for approx. 30 hours on battery power.
- Key switch protected control panel against tampering. Membrane keyboard with digital temperature display and minimum/maximum temperature memory. Control and display sensors protected by safety barriers.
- Warning functions with visual and audible alarm signal in the case of temperature deviations or other malfunctions. Door open alarm after 60 seconds.
- Alarms can be forwarded using a potential-free contact (e.g., to a mobile phone with optional GSM-Module or to a control centre).
- Data documentation can be read via USB interface with KIRSCH Datanet software.
- Antifreeze against sub-zero temperatures.
- Ventilation-enforced refrigerating machine, hermetically sealed, energy saving, low-noise, easy to service.

### Specification

	LABEX® 520 PRO-ACTIVE	LABEX® 720 PRO-ACTIVE
Capacity	500 Liter	700 Liter
Temperature setting	approx. +0 °C to +15 °C	approx. +0 °C to +15 °C
Voltage	220 – 240 V, 50 Hz	220 – 240 V, 50 Hz
Power consumption	234 Watt	237 Watt
Normal consumption	1,2 kWh/24 h	1,23 kWh/24 h
Admissible ambient temperature	from +10 °C to +38 °C	from +10 °C to +38 °C
Heat emission (max.)	543 Watt	545 Watt
Exterior dimensions (including door handle and distance from wall)	w x d x h = 77 x 76 x 193- 196 cm	w x d x h = 77 x 98 x 193- 196 cm
Interior dimensions	w x d x h = * 62 x 57 x 140 cm	w x d x h = * 62 x 77 x 140 cm
Exterior dimensions with door open at 90°	w x d = 77 x 144 cm	w x d = 77 x 165 cm
Shelfsize	w x d = 59 x 45 cm	w x d = 59 x 65 cm
Max. load shelf	40 kg	40 kg
Weight	netto 120 kg, brutto 148 kg	netto 145 kg, brutto 174 kg

## Optional equipment

- Glass door with lock.
- Adjustable feet to compensate uneven floors.
- Drawer conductive on roller runners Only for LABEX® 520 PRO-ACTIVE: w x d x h = 57 x 39 x 5.6 cm(a maximum of twelve drawers is possible).
- Additional length and cross dividers (for drawer).
- Additional shelf on rails or brackets.
- Basket on rails LABEX® 520 PRO-ACTIVE: w x d x h = 60 x 45 x 10 cm, LABEX® 720 PRO-ACTIVE: w x d x h = 60 x 65 x 10 cm.
- Aluminium tray with rails LABEX® 520 PRO-ACTIVE: w x d x h =  $60 \times 40 \times 2.5 \text{ cm}$ , LABEX® 720 PRO-ACTIVE: w x d x h =  $60 \times 65 \times 2.5 \text{ cm}$ .
- Outer housing in stainless steel 4301, longitudinal brushed.
- GSM-Module for alarm text message transmission (e.g., to a mobile phone).
- Water-cooled refrigerating machine.
- Temperature documentation.
  - Temperature sensor PT 100 or PT 1000, with safety barriers and reference body (measuring bottle or cold block) is installed.
  - 4-pin PT 100 or PT 1000 temperature sensor, class 1/3 B, including built-in reference body.
  - Mechanical pen-recording thermometer with two waxed paper strips.